

Installation and operating instructions



POOL - Master 400

Art.No.3002800130

Not suitable for filter pumps with speed control



Function:

The **POOL** Pool Master 400 filter control enables a 400V 3-phase filter pump to be switched on or off in a timed manner. The time of day and the individual switching periods are set in accordance with the enclosed operating instructions of the timer. The selection switch on the front cover is used to:

- (a) Switch the function of the system on or off.

CAUTION: this does not isolate all poles of the control from supply!

- (b) Switch the system to continuous operation or automatic operation (timer) of the filter pump.

In addition, during the operating time of the filter pump the heating of the pool is controlled by the electronic temperature control. The heating is switched off automatically by the internal interlocking during filtering pauses. An adjustment control on the front cover can be used to select the desired temperature of the swimming pool water or turn the heating off.

Another terminal enables accessories to be connected, e.g. feeders. The terminals D/D are floating contacts and can therefore be used as needed. The relay contact between the terminals D/D is closed during the filtering times and open outside the filtering times. Currents of up to 230V and outputs of up to 400W ($\cos \varphi = 1$) can be put on this contact.

The terminals for the motor winding protection contact (WSK) enable a motor winding protection contact switch to be connected, which is integrated into the motor winding of the filter pump. If this contact opens, e.g. as result of the motor winding becoming excessively hot, the filter pump and with it the heating and the feeder are switched off automatically as well. As soon as the motor winding protection contact closes after the motor has cooled down, the units will switch on again automatically. A manual reset is not necessary. The terminals WSK are allocated 230V.

Control lamps in the front cover indicate that the filter pump and the heating are operating, enabling verification to be made at any time.

The filter pump is protected from overload by an electronic motor protection (current range infinitely variable up to 8A).

Technical data:

Dimensions:	220mm x 219mm x 100mm		
Operating voltage:	400V/50Hz		
Power consumption of control system:	approx. 5VA		
Not suitable for filter pumps with speed control			
Switching capacity:	Pump:	max. 3,0 kW (AC3)	
	Heating:	max. 0,4 kW (AC1)	
Protection class:	IP 40		

Installation:


The control unit must be installed protected from moisture in accordance with its protection class. The ambient temperature during operation may be between 0°C and 40°C and should be as constant as possible. The rel. Humidity at the installation location must not exceed 95%. Condensation must not occur. Direct heat or solar radiation to the device should be avoided. The power supply of the unit must be connected via an all-pole main switch with a contact gap of at least 3 mm and an earth leakage protection switch with $I_{FN} \leq 30\text{mA}$.

The unit must be isolated from supply before opening the case.


Electrical connection:

The electrical connection, and adjustment work and service may only be carried out by an approved electrician! The following terminal diagram and the currently applicable safety regulations must be observed.

When using a 400V three-phase current pump:



When using a 230V alternating current pump:




This control is not suitable for the connection of a filter pump with speed control. For such pumps we have other controls in our product range

The bridge between the two terminals labelled *WSK* inserted at the factory must be removed when connecting a motor winding protection contact. If no connection is made, it must be left screwed in place.

A **floating contact** for connecting the feeder is provided at terminals *D/D*. This contact is always closed when the filter pump is operating.

A 2A fine-wire fuse in the terminal box protects the electronic control together with the heating.


Electronic motor protection:



The 3-phase filter pump is protected from damage resulting from overload by an electronic motor protection. To do so the motor protection needs to be set to the nominal current of the filter pump (see name plate of the pump). If the nominal current of the filter pump is not known, the motor protection can be set using the following procedure:


1. Turn the adjustment screw of the motor protection in the terminal box clockwise up to the stop.
2. Switch the pump on
3. Turn the adjustment screw slowly counter clockwise until the motor protection trips and the red fault message comes on.
4. Turn the adjustment screw clockwise by some degrees (approx. 10%).
5. Release the motor protection with the black key: the fault message goes off and the filter pump runs.

Temperature control:



The electronic temperature control and the temperature detector have been aligned to each other at the factory. If the detector is replaced, a new alignment can be made using a potentiometer inside the equipment. If, due to an unsuitable installation position of the temperature detector, the water temperature does not match the desired temperature, this can also be adjusted using the same potentiometer.


The temperature detector is supplied with a 1.5m cable as standard. If required this can be extended up to 20m. To rule out interference avoid installing the detector cable in the vicinity of supply cables.




Since an exact temperature control is only performed when there is good heat transfer between temperature detector and swimming pool water, an osf immersion sleeve R 1/2 " (product code 3200200001) must be installed in the pipe system.

Operation of the timer

Set the time



Set switching time



Further information can be found on the Internet at the following address:
<https://osf.de/download/documents/doclist.php?device=PM-400&subdir=none>



We hope you enjoy relaxing in your swimming pool.

OSF Hansjürgen Meier
Elektrotechnik und Elektronik GmbH & Co KG
Eichendorffstraße 6
D-32339 Espelkamp
E-Mail: info@osf.de
Internet: www.osf.de